FUZYPRO Data Logger

PHTEMP101 pH and Temperature Recorder

FEATURES

- Low cost
- Miniature size
- User-friendly
- Automatic temperature compensation
- Programmable start time
- Real-time operation
- Programmable engineering units
- N.I.S.T. traceable

APPLICATIONS


- Surface and ground water quality monitoring
- Environmental/wetlands
- Industrial influent/effluent
- Water districts and municipal
- Process water quality
- Recreation/park management
- Pulp and paper industry
- Wastewater monitoring




The PHTEMP101 is a miniature, battery powered, stand alone pH and temperature recorder. This is an all-in-one compact, portable, easy to use device that will measure and record up to 13,107 measurements per channel. The PHTEMP101 will directly connect to many commonly used pH electrodes, in addition, the PHTEMP101 will also directly connect to many ORP electrodes. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged. The device can be started and stopped directly from your computer and its small size allows it to fit almost anywhere. The PHTEMP101 makes data retrieval quick and easy. Simply plug it into an empty com port and our user-friendly software does the rest.

SOFTWARE

FUZYPRO,s Data Recorder
Software is an easy to use
Windows-based software package
that allows the user to effortlessly
collect, display and analyze data.
A variety of powerful tools allow
you to examine, export, and print
professional looking data with just
a click of the mouse.





Temperature*

Measurement Range: -200 °C to +850 °C (0 to +5000 Ω)

Resolution: 0.01 °C (0.001 Ω)

Calibrated Accuracy: ±0.1 °C @25 °C ambient (±0.015 Ω) Input Connection: Removable screw terminal; 2,3 or 4-

wire interface

pН

Measurement Range: 0.00 to 14.00 pH (-1000 to +1000 mV)

Resolution: 0.01 pH (0.1 mV)

Calibrated Accuracy: ±0.1 pH (±1 mV) Input Connection: Female BNC jack

Input Resistance: 10¹² Ω typical

Start Time: Software programmable start time

and date, up to six months in

advance

Real Time Recording: May be used with PC to monitor and

record data in real time

Memory: 13,107 readings per channel

Reading Interval: 1 reading every 2 seconds to 1 every 12 hours

Calibration: Digital calibration through software

Calibration Date: Automatically recorded within device

Power: 9V lithium or alkaline battery included

User Replaceable Battery: 1 year typical with lithium battery at 25 °C

Data Format: Date and time stamped °C, °F, °K, °R, Ω; pH, V,

mV, engineering units specified through software

Time Accuracy: ±1 minute/month (at 25 °C; RS232 cable not in use)

Computer Interface: PC serial or RS232C COM (Interface cable

required); 2,400 baud

Software: Windows 95/98/ME/NT/2000/XP based software

Operating Environment: -5 °C to +50 °C, 5 to 95 %RH (non-condensing)

Dimensions: 4.5" x 2.4" x 1.0" x (114mm x 61mm x 25mm)

Weight: 4 oz (120 g)

*Temperature specifications based on ideal 100 Ω Pt RTD compliant with IEC 751 (1983) and ITS-90, 5000 Ω FSR **For use in harsh environments, this device must be well protected from weather, steam and harsh chemicals

PHTEMP101 SOFTWARE FEATURES

Simultaneously analyze data from Multiple Graphs:

several units or deployments; easily

switch to a single data series

Real-Time Recording: Collect and display data in real-time

while continuing to log

One click displays readings by time, **Graphical Cursor:**

value, parameter or sample number

Data Table: Instantly access tabular view for

detailed dates, times, values, and annotations

Autoscale function fits data to the Scaling Options:

screen, or allows user to manually

enter their own values

Change colors, line styles, plotting Formatting Options:

options, show or hide channels in an

instant

Statistics: Calculate averages, min, max, standard

deviation, and mean kinetic temperature with

the touch of a button

Export Data: Export data in a variety of common formats, or

switch to Excel with a single click

Fully digital calibration function automatically Calibration:

stores parameters in device

Logger Configuration: Easy set up and launch of data loggers with

immediate or delayed start, preferred sample

rate, and device ID

Communications: Automatically sets up communications port, or

lets user set configuration

Automatically print graphical or tabular data Printing:

***As part of our commitment to continuous product improvement, FUZYPRO reserves the right to change product specifications without notice

ORDERING INFORMATION

Model Description

PHTEMP101 pH and Temperature Recorder

IFC101 Software, manual and 9-pin computer

interface cable

N.I.S.T. Cert N.I.S.T. Calibration Certificate

ASK ABOUT OUR OTHER DATA RECORDERS

Temperature Humidity **Pressure** Bridge/Strain Current Pulse/Event Voltage

pН Level Shock/Vibration Submersible Intrinsically Safe

RF Transmitters Multi-parameter